

Монитор, Клавиатура, сенсорная панель, Ящик 1 U

Data Solutions



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



FEATURES

Выдвижное шасси для 17-дюймового цветного TFT-монитора, 1 U (разрешение 1280 x 1024; подключается к интерфейсу VGA)

Клавиатура с различными раскладками (подключается через USB)

Встроенная сенсорная панель (подключается через USB)

Напряжение питания: Широкополосный вход (номинальное напряжение сети от 110 до 240 В перем. тока), напряжение питания 12, 24 и 48 В пост. тока – по запросу

Регулируемая глубина крепления с разным шагом серверной панели/монтажного профиля; Глубина монтажа (размер с = интервал 19-дюймового профиля): размер с 470 ... 740 мм

SPECIFICATIONS

Глубина мм: 470mm

Product Type: Cabinet/Rack Drawer

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Type	Works With
60118-580	1U	1	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets
60118-581	1U	1	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets
60118-582	1U	1	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets

Table 2/2

Catalog Number	Keyboard Type
60118-580	QWERTY UK
60118-581	QWERTZ
60118-582	AZERTY

ADDITIONAL PRODUCT DETAILS

Другие варианты исполнения по запросу. С трекболом или цифровой клавиатурой.

Другие раскладки клавиатуры см. в руководстве пользователя.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE