

Single Temperature Sensor

Data Solutions



Single Temperature Probe Sensor for nVent SCHROFF RackPower PDU's.

FEATURES

Single Temperature Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +- 2 %

SPECIFICATIONS

Table 1/1

Catalog Number	Works With	Высота мм	Package Quantity	Plug Type	Removable Input Cable
EA9102	RackPower	270mm	1	RJ45	Нет

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE