

Блок розеток, IEC C13, со встроенным измерением мощности

Data Solutions



Блок распределения питания со встроенным измерением мощности. Полученные данные о мощности отображаются на встроенном дисплее.

CERTIFICATIONS



FEATURES

При установке панель электропитания можно развернуть в любую сторону (с шагом 90°)

Монтажная высота 1 U

Встроенная функция измерения и отображение на локальном дисплее

Панель электропитания с розетками IEC 60320-C13

Возможен горизонтальный и вертикальный монтаж

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Color	Switched Outlets	Длина мм
60110-296	Панели электропитания	IEC C13	8	Серый	Да	438.5mm

Table 2/2

Catalog Number	Voltage AC	Глубина мм	Material	Package Quantity
60110-296	230V	44mm	Алюминий, Polyamide	1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE