

панель электропитания, UTE, с входом Wieland®

Data Solutions



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Эта панель электропитания с алюминиевым шасси размером 1 U x 1 U легко интегрируется в шкаф. Разъем Wieland обеспечивает простую комбинацию с различными входными кабелями питания.

CERTIFICATIONS



FEATURES

Вход: штекер Wieland® GST 18

Во время установки панель электропитания можно поворачивать во всех направлениях (с шагом 90°)

Выход: розетки UTE

Горизонтальная или вертикальная установка

Установочная высота 1 U

В соответствии с NFC 61-303

Монтажная высота 1 U

В соответствии с NFC 61-303

SPECIFICATIONS

Длина мм: 438.5mm

Material: Алюминий; Polyamide

Product Type: Панели электропитания

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-347	UTE	8	Нет	230V		1
60110-348	UTE	8	Нет	230V		1
60110-346	UTE	8	Нет	230V		1
60110-355	UTE	6	Нет	230V	Overcurrent Protection	1
60110-357	UTE	6	Нет	230V	Overcurrent Protection	1
60110-356	UTE	6	Нет	230V	Overcurrent Protection	1

Table 2/2

Catalog Number	Color	Глубина мм	Finish
60110-347	Черный	44mm	Anodized
60110-348	Красный	44mm	Anodized
60110-346	White	44mm	Anodized
60110-355	White	44mm	Anodized
60110-357	Красный	44mm	Anodized
60110-356	Черный	44mm	Anodized

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE