

# Varistar CP Base/Plinth

## Data Solutions

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



### FEATURES

2 support profiles, for front and rear

Static load-carrying capacity 1000 kg

### SPECIFICATIONS

**Product Type:** Cabinet/Rack Base

**Material:** Сталь

Table 1/2

Catalog Number	Высота мм	Ширина мм	Package Quantity	Color	Color Code	Глубина мм
24630-034	100mm	600mm	1	Black Grey	RAL 7021	600mm
24630-035	100mm	800mm	1	Black Grey	RAL 7021	
24630-036	200mm	600mm	1	Black Grey	RAL 7021	
24630-037	200mm	800mm	1	Black Grey	RAL 7021	
24630-064	100mm	600mm	1	Black Grey	RAL 7021	

CatalogNumber	Высота мм	Ширина мм	Package Quantity	Color	Color Code	Глубина мм
24630-065	100mm	800mm	1	Black Grey	RAL 7021	
24630-066	200mm	600mm	1	Black Grey	RAL 7021	
24630-067	200mm	800mm	1	Black Grey	RAL 7021	

Table 2/2

Catalog Number	Finish	Type
24630-034	Powder Coated	Base Plinth, C перфорацией
24630-035	Powder Coated	Base Plinth, C перфорацией
24630-036	Powder Coated	Base Plinth, C перфорацией
24630-037	Powder Coated	Base Plinth, C перфорацией
24630-064	Powder Coated	Base Plinth, Plain
24630-065	Powder Coated	Base Plinth, Plain
24630-066	Powder Coated	Base Plinth, Plain
24630-067	Powder Coated	Base Plinth, Plain

## ADDITIONAL PRODUCT DETAILS

Please order side trims separately.

Cannot be used in conjunction with castors

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**