

HFBT nVent ERIFLEX Flexibar Bending Tool



CERTIFICATIONS



FEATURES

Allows the user to bend nVent ERIFLEX Flexibar into custom shapes for an efficient installation

Easy-to-use tool bends all sizes of nVent ERIFLEX Flexibar quickly without damage to the insulation

Portable tool can be used on the jobsite or attached to a workbench

Includes tool box

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Bending Radius	Bending Angle	Глубина мм	Height
HFBT	558920	Сталь	10mm	180 ° Max	120mm	215 mm

Table 2/2

Catalog Number	Article Number	Width	Unit Weight
HFBT	558920	345 mm	7 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE