

# nVent ERIFLEX IFBS Reinforcement Kit for High Short-Circuit



High short-circuit kit designed to upgrade the nVent ERIFLEX IFBS so it may withstand high short-circuit values up to 130kA peak. This kit includes two strut nuts, two M8 – CHC Head Screws (75mm), two M8 – CHC Head Screws (40mm), and five reinforced spacers.

#### **CERTIFICATIONS**



## **FEATURES**

Designed to reinforce the nVent ERIFLEX IFBS Support Kit

Can be mounted on a C-shaped profile

Low smoke, halogen free, flame retardant and resistant to high temperatures

IEC® 61439-1 certified and RoHS compliant

### **SPECIFICATIONS**

**Complies With:** IEC® 60695-2-11 (Glow Wire Test 960 °C);IEC® 61439.1

Flammability Rating: UL® 94V-0
Working Temperature: -40 to 130 °C

			Table 1/2			
Catalog Number	Article Number	Material	For Use With	Conductor Type	A	В


IFBS20SC32	553597	Сталь, Glass Fibre Reinforced Polyamide	ISBF20, ISBF24, ISBF32	Flexibar, IBSB Advanced	11 mm	15 mm
IFBS40SC63	553598	Сталь, Glass Fibre Reinforced Polyamide	ISBF40, ISBF50, ISBF63	Flexibar	23 mm	15 mm

Table 2/2					
Catalog Number	Article Number	Width (W)	Height (H)	Длина мм (L)	Unit Weight
IFBS20SC32	553597	19.5 mm	30 mm	40mm	0.33 kg
IFBS40SC63	553598	40 mm	30 mm	40mm	0.39 kg

# ADDITIONAL PRODUCT DETAILS

The kit includes: 2 Strut Nuts, 2 CHC Head Screws 75mm length M8, 2 CHC Head Screws 45mm length M8, 5 Reinforced Spacers

Recommendation - Max Distance Between Supports (mm)				
lpk (Short-Circuit Current Peak - kA)	IFBS Support Kit 20/24/32 + High Short-Circuit Kit	IFBS Support Kit 40/50/63 + High Short-Circuit Kit		
10	1000	1000		
20	1000	1000		
30	1000	1000		
40	740	1000		
50	480	1000		
60	330	770		
70	240	570		
80	190	430		
90	150	340		
100	120	280		
110	-	230		
120	-	190		
130	-	160		





#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

# Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY TRACHTE ERICO HOFFMAN ILSCO SCHROFF**