

SBS Isolating Silicone Sleeve



CERTIFICATIONS



FEATURES

Resistant to high temperature

Cost effective sleeve for insulation

High flexibility

Halogen free

SPECIFICATIONS

Insulation Voltage:	2.5kV
Max Working Voltage, IEC (Ui):	690
Max Working Voltage, UL (Vin):	690
Material:	Fiberglass;Silicone
Flammability Rating:	UL® 1441 VW-1
Working Temperature:	-60 to 220 °C

Table 1/1

Catalog Number	Article Number	Diameter	Длина мм	Unit Weight
SBS-4	554000	4 mm	100m	0.02 kg

Catalog Number	Article Number	Diameter	Длина мм	Unit Weight
SBS-6	554010	6 mm	100m	0.04 kg
SBS-10	554030	10 mm	100m	0.05 kg
SBS-8	554020	8 mm	100m	0.05 kg
SBS-12	554040	12 mm	100m	0.07 kg
SBS-15	554050	15 mm	25m	0.11 kg
SBS-20	554060	20 mm	25m	0.15 kg
SBS-25	554070	25 mm	30m	0.18 kg
SBS-30	554080	30 mm	30m	0.22 kg

ADDITIONAL PRODUCT DETAILS

Unit weight is per meter (3.28').

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE