


Universal Busbar Support



CERTIFICATIONS



FEATURES

Universal fixing system

Installs quickly and easily

Extremely robust construction

Adjustable arms for easy mounting

Halogen free insulators

SPECIFICATIONS

Max Working Voltage, IEC (Ui):	1000;1500
Complies With:	IEC® 60439.1;IEC® 61439.1;IEC® 60695-2-11 (Glow Wire Test 960 °C)
Flammability Rating:	UL® 94V-0
Working Temperature:	-40 to 130 °C

Table 1/2


Catalog Number	Article Number	Material	Typical Application Current Rating	Busbars per Phase	Busbar Width	Busbar Thickness
----------------	----------------	----------	------------------------------------	-------------------	--------------	------------------

UBS4-5T	551020	Сталь, Glass Fibre Reinforced Polyamide	3500 A	1 - 4	30 - 125 mm	5 mm
UBS2-10T	551080	Сталь, Glass Fibre Reinforced Polyamide	3600 A	1 - 2	30 - 120 mm	10 mm

Table 2/2

Catalog Number	Article Number	Width (W)	A	B	C	D
UBS4-5T	551020	375 - 575 mm	350 - 550 mm	176 mm	307 mm	110 mm
UBS2-10T	551080	375 - 575 mm	350 - 550 mm	176 mm	307 mm	110 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE