

Секционная дверь, 150x600, Низкоуглеродистая сталь, Замок с двумя бородками 3 мм, IP44

CATALOG NUMBER

DP01506R5



Partial doors allow for many different, easily accessible configurations of separate compartments, within the enclosure.

FEATURES

Description: To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CHDK. Equipped with double-bit 3 mm lock (1 lock up to 400 mm, over 400 mm height 2 locks).

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44.

Pack quantity: 1 door with hinges, locks and mounting accessories.

Mounting requirements: Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

PRODUCT ATTRIBUTES

Высота мм: 150mm

Ширина мм: 600mm

Глубина мм: 17mm

Enclosure Material: Mild Steel

Product Family: Free-Standing

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE