


, WO60

1-pole busbar support, for a wide range of busbar sizes.



FEATURES

Description: PE/N-support. Individually mountable. N-PE connection easy to make.

Rated voltage: 690 V

Rated isolation voltage U_i : 1000 V

Rated surge voltage U_{imp} : 6 kV

Short circuit withstand: 14 kA (max 400 mm distance between supports)

SPECIFICATIONS

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Material	Finish	Color
01356	20mm	65mm	50mm	Plastic, Сталь	Smooth	Light Gray
01601	20mm	164mm	50mm	Plastic, Сталь	Smooth	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE