

Combined Mounting Kit for Chassis

Power Utilities



The combined mounting enable the option to split a 6 U high subrack or case in 2 x 3 U and 6 U sections. Different versions are available.

CERTIFICATIONS



FEATURES

Designed to accept Euroboards (100 mm high) and double Euroboards (233.35 mm high)

Subdivision of the 6 U assembly area into: 2 x 3 U, 1 x 6 U

SPECIFICATIONS

Table 1/2

Catalog Number	Package Quantity	Rack Width 1	Rack Width 2	Product Family	Product Type	Rack Height
24562-463	1	63 HP	19 HP	EuropacPRO	Mounting Kit	6 U
24562-442	1	42 HP	40 HP	EuropacPRO	Mounting Kit	6 U
24562-440	1	40 HP	42 HP	EuropacPRO	Mounting Kit	6 U
24562-484	1	84 HP		EuropacPRO	Mounting Kit	6 U

CatalogNumber	Package Quantity	Rack Width 1	Rack Width 2	Product Family	Product Type	Rack Height
24562-420	1	20 HP	62 HP	EuropacPRO	Mounting Kit	6 U

Table 2/2

Catalog Number	Type	Works With
24562-463	Combined	Блочный каркас
24562-442	Combined	Блочный каркас
24562-440	Combined	Блочный каркас
24562-484	Combined	Блочный каркас
24562-420	Combined	Блочный каркас

ADDITIONAL PRODUCT DETAILS

Please order separately: Front panel 6 U, 2 HP to cover the strut.

The following guide rails cannot be used: type "accessory", type "accessory, strengthened" and type "for 4.4" PCB".

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE