

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Power Utilities

Non-shielded subrack for backplane mounting.



CERTIFICATIONS



FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Глубина мм	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-131	3 U	175 mm	1	Объединительная плата	160 mm	Нержавеющая сталь
24563-132	3 U	235 mm	1	Объединительная плата	160 mm, 220 mm	Нержавеющая сталь
24563-133	3 U	295 mm	1	Объединительная плата	160 mm, 220 mm, 280 mm	Нержавеющая сталь
24563-134	3 U	355 mm	1	Объединительная плата	160 mm, 220 mm, 280 mm, 340 mm	Нержавеющая сталь
24563-135	3 U	415 mm	1	Объединительная плата	160 mm, 220 mm, 280 mm, 340 mm	Нержавеющая сталь
24563-136	3 U	475 mm	1	Объединительная плата	160 mm, 220 mm, 280 mm, 340 mm	Нержавеющая сталь
24563-431	6 U	175 mm	1	Объединительная плата	160 mm	Нержавеющая сталь
24563-432	6 U	235 mm	1	Объединительная плата	160 mm, 220 mm	Нержавеющая сталь
24563-433	6 U	295 mm	1	Объединительная плата	160 mm, 220 mm, 280 mm	Нержавеющая сталь
24563-434	6 U	355 mm	1	Объединительная плата	160 mm, 220 mm, 280 mm, 340 mm	Нержавеющая сталь
24563-435	6 U	415 mm	1	Объединительная плата	160 mm, 220 mm, 280 mm, 340 mm	Нержавеющая сталь
24563-436	6 U	475 mm	1	Объединительная плата	160 mm, 220 mm, 280 mm, 340 mm	Нержавеющая сталь

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24563-131	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-132	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP

CatalogNumber	HandleIncluded	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24563-133	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-134	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-135	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-136	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-431	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-432	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-433	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-434	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-435	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP
24563-436	Нет	Rack	IEC 60297-3-103	Нет	Subrack/Chassis	84 HP

Table 3/3

Catalog Number	Static Load
24563-131	11 kgf
24563-132	11 kgf
24563-133	11 kgf
24563-134	11 kgf
24563-135	11 kgf
24563-136	11 kgf
24563-431	11 kgf

Catalog Number	Static Load
24563-432	11 kgf
24563-433	11 kgf
24563-434	11 kgf
24563-435	11 kgf
24563-436	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE