

# EuropacPRO 19" Subrack Kit for Railway, Retrofit Shielding, EN 50155

## Power Utilities



Subrack for Railway applications, conform to EN50155 standard, non-shielded.

## CERTIFICATIONS



## FEATURES

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

Modifications such as cutouts, different finishes or dimensions available

IP 20, in accordance with IEC 60529

The double 19" screwing position adds to additionally safety (NFF standard)

Supplied as space-saving flat-pack

## SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Глубина мм | Package Quantity | For Mounting | Board Depth | Shock and Vibration Tolerance |
|----------------|-------------|------------|------------------|--------------|-------------|-------------------------------|
|----------------|-------------|------------|------------------|--------------|-------------|-------------------------------|

|           |     |        |   |                       |        |             |
|-----------|-----|--------|---|-----------------------|--------|-------------|
| 21500-078 | 6 U | 235 mm | 1 | Объединительная плата | 220 mm | 5 g (force) |
| 21500-077 | 3 U | 235 mm | 1 | Объединительная плата | 220 mm | 5 g (force) |

Table 2/3

| Catalog Number | Handle Included | Mounting | Complies With                          | EMC Shielding | Product Type    | Rack Width |
|----------------|-----------------|----------|----------------------------------------|---------------|-----------------|------------|
| 21500-078      | Да              | Rack     | IEC 60297-3-103, EN 50155 part 12.2.11 | Нет           | Subrack/Chassis | 84 HP      |
| 21500-077      | Да              | Rack     | IEC 60297-3-103, EN 50155 part 12.2.11 | Нет           | Subrack/Chassis | 84 HP      |

Table 3/3

| Catalog Number | Static Load |
|----------------|-------------|
| 21500-078      | 15 kgf      |
| 21500-077      | 15 kgf      |

## ADDITIONAL PRODUCT DETAILS

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**