

EuropacPRO 19" Subrack Kit for Railway, Shielded, SNCF

Power Utilities

Subrack for Railway applications, conform to SNCF Standard.



CERTIFICATIONS



FEATURES

SNCF listed, EuropacPRO-fer, tested to NF F 61-005 and NF F 60-002

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

Lateral support bars to NFF standard facilitate insertion of subrack into the (cabinet) frame. The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	For Mounting	Board Depth	Shock and Vibration Tolerance
21500-071	6 U	36 HP	1	Объединительная плата	220 mm	5 g (force)
21500-068	3 U	36 HP	1	Объединительная плата	220 mm	5 g (force)
21500-030	3 U	84 HP	1	Объединительная плата	220 mm	5 g (force)
21500-028	6 U	84 HP	1	Объединительная плата	220 mm	5 g (force)

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	Глубина мм	EMC Shielding	Product Type
21500-071	Да	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Да	Subrack/Chassis
21500-068	Да	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Да	Subrack/Chassis
21500-030	Да	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Да	Subrack/Chassis
21500-028	Да	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Да	Subrack/Chassis

Table 3/3

Catalog Number	Static Load	Certifications
21500-071	15 kgf	RoHS
21500-068	15 kgf	RoHS
21500-030	15 kgf	RoHS, SNCF

Catalog Number	Static Load	Certifications
21500-028	15 kgf	RoHS, SNCF

ADDITIONAL PRODUCT DETAILS

Fer = ferroviaire = French Railways, 1 T = 4 HP = 20.32 mm.

Receptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE