

Front Panel, Anodized, Unshielded, Screw Assembly

Power Utilities

Anodized front panel, unshielded version, Al, 2.5 mm.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, anodized

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-416	2 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-494	3 U	42 HP	1	Screw-on Front	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-506	3 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-596	4 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-764	6 U	42 HP	1	Screw-on Front	Anodized	Anodized
30807-771	6 U	63 HP	1	Screw-on Front	Anodized	Anodized
30807-776	6 U	84 HP	1	Screw-on Front	Anodized	Anodized
30808-067	3 U	63 HP	1	Screw-on Front	Anodized	Anodized
30810-432	3 U	2 HP	5	Screw-on Front	Anodized	Anodized
30818-741	6 U	2 HP	5	Screw-on Front	Anodized	Conductive
30807-481	3 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-482	3 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-483	3 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-484	3 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-485	3 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-487	3 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-496	3 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-501	3 U	14 HP	5	Screw-on Front	Anodized	Anodized
30807-508	3 U	3 HP	5	Screw-on Front	Anodized	Anodized
30807-509	3 U	7 HP	5	Screw-on Front	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-510	3 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-778	6 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-777	6 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-752	6 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-753	6 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-755	6 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-757	6 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-758	6 U	14 HP	5	Screw-on Front	Anodized	Conductive
30807-766	6 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-779	6 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-780	6 U	16 HP	5	Screw-on Front	Anodized	Anodized
30807-833	6 U	7 HP		Screw-on Front	Anodized	Anodized

Table 2/3

Catalog Number	Treated Edges	Complies With	EMC Shielding	Высота мм	Material	Product Type
30807-416	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	84 mm	Алюминий	Передняя панель
30807-494	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-506	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Высота мм	Material	Product Type
30807-596	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	172.9 mm	Алюминий	Передняя панель
30807-764	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-771	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-776	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30808-067	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30810-432	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30818-741	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-481	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-482	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-483	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-484	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-485	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-487	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-496	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-501	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Высота мм	Material	Product Type
30807-508	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-509	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-510	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий	Передняя панель
30807-778	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-777	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-752	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-753	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-755	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-757	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-758	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-766	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-779	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-780	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель
30807-833	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий	Передняя панель

Table 3/3

Catalog Number	Type	Ширина мм	Certifications
----------------	------	-----------	----------------

30807-416	Front Panel without Handle	426.4 mm	RoHS
30807-494	Front Panel without Handle	213 mm	RoHS
30807-506	Front Panel without Handle	426.4 mm	RoHS
30807-596	Front Panel without Handle	426.4 mm	
30807-764	Front Panel without Handle	213 mm	RoHS
30807-771	Front Panel without Handle	319.7 mm	RoHS
30807-776	Front Panel without Handle	426.4 mm	RoHS
30808-067	Front Panel without Handle	319.7 mm	RoHS
30810-432	Front Panel without Handle	9.8 mm	RoHS
30818-741	Front Panel without Handle	9.8 mm	RoHS
30807-481	Front Panel without Handle	20 mm	RoHS
30807-482	Front Panel without Handle	30.1 mm	RoHS
30807-483	Front Panel without Handle	50.5 mm	RoHS
30807-484	Front Panel without Handle	40.3 mm	RoHS
30807-485	Front Panel without Handle	60.6 mm	RoHS
30807-487	Front Panel without Handle	106.3 mm	RoHS
30807-496	Front Panel without Handle	141.9 mm	RoHS
30807-501	Front Panel without Handle	70.8 mm	RoHS
30807-508	Front Panel without Handle	14.9 mm	RoHS

30807-509	Front Panel without Handle	35.2 mm	RoHS
30807-510	Front Panel without Handle	25 mm	RoHS
30807-778	Front Panel without Handle	20 mm	RoHS
30807-777	Front Panel without Handle	25 mm	RoHS
30807-752	Front Panel without Handle	30.1 mm	RoHS
30807-753	Front Panel without Handle	50.5 mm	RoHS
30807-755	Front Panel without Handle	60.6 mm	RoHS
30807-757	Front Panel without Handle	106.3 mm	RoHS
30807-758	Front Panel without Handle	70.8 mm	RoHS
30807-766	Front Panel without Handle	141.9 mm	RoHS
30807-779	Front Panel without Handle	40.3 mm	RoHS
30807-780	Front Panel without Handle	80.9 mm	RoHS
30807-833	Front Panel without Handle	35.2 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE