

Front Panel, Anodized With Untreated Edges, Unshielded

Power Utilities



Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.

CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30818-271	2 U	84 HP	1	Her	Screw-on Front	Anodized
30818-310	3 U	42 HP	1	Her	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30818-331	3 U	63 HP	1	Her	Screw-on Front	Anodized
30818-352	3 U	84 HP	1	Her	Screw-on Front	Anodized
30818-434	4 U	84 HP	1	Her	Screw-on Front	Anodized
30818-556	6 U	42 HP	1	Her	Screw-on Front	Anodized
30818-577	6 U	63 HP	1	Her	Screw-on Front	Anodized
30818-598	6 U	84 HP	1	Her	Screw-on Front	Anodized
30810-433	3 U	2 HP	5	Her	Screw-on Front	Anodized
30818-747	6 U	2 HP	5	Her	Screw-on Front	Anodized
30818-272	3 U	3 HP	5	Her	Screw-on Front	Anodized
30818-273	3 U	4 HP	5	Her	Screw-on Front	Anodized
30818-274	3 U	5 HP	5	Her	Screw-on Front	Anodized
30818-275	3 U	6 HP	5	Her	Screw-on Front	Anodized
30818-276	3 U	7 HP	5	Her	Screw-on Front	Anodized
30818-277	3 U	8 HP	5	Her	Screw-on Front	Anodized
30818-279	3 U	10 HP	5	Her	Screw-on Front	Anodized
30818-281	3 U	12 HP	5	Her	Screw-on Front	Anodized
30818-282	3 U	14 HP	5	Her	Screw-on Front	Anodized
30818-284	3 U	16 HP		Her	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30818-289	3 U	21 HP	5	Нет	Screw-on Front	Anodized
30818-296	3 U	28 HP	5	Нет	Screw-on Front	Anodized
30818-517	6 U	3 HP		Нет	Screw-on Front	Anodized
30818-518	6 U	4 HP	5	Нет	Screw-on Front	Anodized
30818-519	6 U	5 HP	5	Нет	Screw-on Front	Anodized
30818-520	6 U	6 HP	5	Нет	Screw-on Front	Anodized
30818-521	6 U	7 HP	5	Нет	Screw-on Front	Anodized
30818-522	6 U	8 HP	5	Нет	Screw-on Front	Anodized
30818-524	6 U	10 HP	5	Нет	Screw-on Front	Anodized
30818-526	6 U	12 HP	5	Нет	Screw-on Front	Anodized
30818-528	6 U	14 HP	5	Нет	Screw-on Front	Anodized
30818-530	6 U	16 HP	5	Нет	Screw-on Front	Anodized
30818-535	6 U	21 HP	5	Нет	Screw-on Front	Anodized
30818-542	6 U	28 HP	5	Нет	Screw-on Front	Anodized

Table 2/3

Catalog Number	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм	Material
30818-271	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	84 mm	Алюминий
30818-310	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм	Material
30818-331	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-352	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-434	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	172.9 mm	Алюминий
30818-556	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-577	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-598	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30810-433	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-747	Anodized	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-272	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-273	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-274	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-275	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-276	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-277	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-279	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм	Material
30818-281	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-282	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-284	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-289	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-296	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4 mm	Алюминий
30818-517	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-518	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-519	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-520	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-521	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-522	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-524	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-526	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-528	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-530	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм	Material
30818-535	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий
30818-542	Anodized	Нет	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8 mm	Алюминий

Table 3/3

Catalog Number	Product Type	Type	Ширина мм	Certifications
30818-271	Передняя панель	Front Panel without Handle	426.4 mm	RoHS
30818-310	Передняя панель	Front Panel without Handle	213 mm	RoHS
30818-331	Передняя панель	Front Panel without Handle	319.7 mm	RoHS
30818-352	Передняя панель	Front Panel without Handle	426.4 mm	RoHS
30818-434	Передняя панель	Front Panel without Handle	426.4 mm	RoHS
30818-556	Передняя панель	Front Panel without Handle	213 mm	RoHS
30818-577	Передняя панель	Front Panel without Handle	319.7 mm	RoHS
30818-598	Передняя панель	Front Panel without Handle	426.4 mm	RoHS
30810-433	Передняя панель	Front Panel without Handle	9.8 mm	RoHS
30818-747	Передняя панель	Front Panel without Handle	9.8 mm	RoHS
30818-272	Передняя панель	Front Panel without Handle	14.9 mm	RoHS
30818-273	Передняя панель	Front Panel without Handle	20 mm	RoHS
30818-274	Передняя панель	Front Panel without Handle	25 mm	RoHS
30818-275	Передняя панель	Front Panel without Handle	30.1 mm	RoHS
30818-276	Передняя панель	Front Panel without Handle	35.2 mm	RoHS

Catalog Number	Product Type	Type	Ширина мм	Certifications
30818-277	Передняя панель	Front Panel without Handle	40.3 mm	RoHS
30818-279	Передняя панель	Front Panel without Handle	50.5 mm	RoHS
30818-281	Передняя панель	Front Panel without Handle	60.6 mm	RoHS
30818-282	Передняя панель	Front Panel without Handle	70.8 mm	RoHS
30818-284	Передняя панель	Front Panel without Handle	80.9 mm	
30818-289	Передняя панель	Front Panel without Handle	106.3 mm	RoHS
30818-296	Передняя панель	Front Panel without Handle	141.9 mm	RoHS
30818-517	Передняя панель	Front Panel without Handle	14.9 mm	
30818-518	Передняя панель	Front Panel without Handle	20 mm	RoHS
30818-519	Передняя панель	Front Panel without Handle	25 mm	RoHS
30818-520	Передняя панель	Front Panel without Handle	30.1 mm	RoHS
30818-521	Передняя панель	Front Panel without Handle	35.2 mm	RoHS
30818-522	Передняя панель	Front Panel without Handle	40.3 mm	RoHS
30818-524	Передняя панель	Front Panel without Handle	50.5 mm	RoHS
30818-526	Передняя панель	Front Panel without Handle	60.6 mm	RoHS
30818-528	Передняя панель	Front Panel without Handle	70.8 mm	RoHS
30818-530	Передняя панель	Front Panel without Handle	80.9 mm	RoHS
30818-535	Передняя панель	Front Panel without Handle	106.3 mm	RoHS

Catalog Number	Product Type	Type	Ширина мм	Certifications
30818-542	Передняя панель	Front Panel without Handle	141.9 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE