


Horizontal Rails Threaded Insert, M2.5

Power Utilities



The threaded insert is a metal strip with thread M2.5 and allows the fixing of front panels.

CERTIFICATIONS



FEATURES

The collar screws used for fixing partial-width front panels must be 12.3 mm long

Usable for all horizontal rails

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Width	Package Quantity	Длина мм	Material	Product Family	Product Type
34561-328	28 HP	1	146.82 mm	Сталь	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert

CatalogNumber	Rack Width	Package Quantity	Длина мм	Material	Product Family	Product Type
34561-363	84 HP	1	324.62 mm	Сталь	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert
34561-342	42 HP	1	217.94 mm	Сталь	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert
34561-384	84 HP	1	431.3 mm	Сталь	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert

Table 2/2

Catalog Number	Works With
34561-328	Блочный каркас, Coffrets
34561-363	Блочный каркас, Coffrets
34561-342	Блочный каркас, Coffrets
34561-384	Блочный каркас, Coffrets

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE