

LAN Surge Protector

Power Utilities



CERTIFICATIONS



FEATURES

Rugged, metallic enclosure provides both environmental and electrical shielding

Up to CAT6 and POE (Power Over Ethernet) protection in one product

Simple, bi-directional installation

SPECIFICATIONS

Catalog Number	LANRJ45C6P
Nominal System Voltage (Un)	48 В пост. тока
Max Continuous Operating Voltage (Uc)	50 VDC
Voltage Protection Rating (VPR), L-L	150 V
Voltage Protection Rating (VPR), L-PE	550 V
Nominal Discharge Current (In), L-L	150 A 8/20 µs
Impulse Current (Iimp)	1 kA 10/350 µs

Catalog Number	LANRJ45C6P
Rated Load Current (IL)	1 A
Frequency	250 MHz Max
Temperature	-40 to 80 °C
Enclosure Rating	IP 20
Height (H)	75 mm
Width (W)	19 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE