

RackPower PDU, RP1xxx, 230/400 VAC, 3-phase

Power Utilities

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

FEATURES

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6" with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Color	Длина мм	Voltage AC	Function
RP1450	Панели электропитания	IEC C13, IEC C13/C19	Черный	1490 mm	230 V	Input Monitored
RP1850	Панели электропитания	IEC C13, IEC C13/C19	Черный	1780 mm	230 V	Input Monitored
RP1950	Панели электропитания	IEC C13, IEC C13/C19	Черный	1826 mm	230 V	Input Monitored

Table 2/2

Catalog Number	Глубина мм	Ширина мм
RP1450	55 mm	56 mm
RP1850	55 mm	56 mm
RP1950	75 mm	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE