

19-дюймовая полка для оборудования, 1 U

19-дюймовая полка для оборудования, макс. нагрузка 5 кг.



CERTIFICATIONS



FEATURES

Монтажная высота 1 U

Допустимая статическая нагрузка 5 кг

SPECIFICATIONS

Product Type: Полка с креплением на каркасе

Material: Сталь

Table 1/2

Catalog Number	Ширина мм	Глубина мм	Finish	Package Quantity	Color	Color Code
20118-782	447mm	390mm	Powder Coated	1	Black Grey	RAL 7021
20118-783	447mm	390mm	Powder Coated	1	Light Grey	RAL 7035
20118-781	447mm	390mm	Aluminum-Zinc Plated	1		

Table 2/2

Catalog Number	Type	Quick Ship
20118-782	Equipment Shelf	No
20118-783	Equipment Shelf	No
20118-781	Equipment Shelf	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE