

19" монтажная рейка

Простая установка для подключения к сети, обеспечивающей надежное газонепроницаемое соединение между контактом и проводником.



CERTIFICATIONS



FEATURES

Монтажная высота 1 U

Для сборки кабельных каналов и блоков соединителей (например, LSA+ или Infra+)

SPECIFICATIONS

Product Type: Bracket

Material: Сталь

Table 1/1

Catalog Number	Глубина мм	Package Quantity	Finish	Type	Works With	Quick Ship
30118-802	70mm	1	Powder Coated	Mounting Bracket	LSA+ Guide Rails	No
30118-803	170mm	1	Powder Coated	Mounting Bracket	LSA+ Guide Rails	No

ADDITIONAL PRODUCT DETAILS

Монтажный комплект для сборки на 19 дюймов заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE