

19-дюйм. нагнетательный вентилятор, 2 U, Диаметральный

Лоток вентилятора с тангенциальным нагнетательным вентилятором.



CERTIFICATIONS



FEATURES

2 варианта. - LE1: 19-дюймовое крепление на винтах, вентиляторный блок шире 19 дюймов - LE2: уменьшенная ширина 19 дюймов, для простой сборки

Высокая производительность

Встроенная фильтренная прокладка

SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage AC	Package Quantity	Material	Quick Ship
60713-001	230V	1	Polyamide 66, Polypropylene	No
60713-004	115V	1	Polyamide 66, Polypropylene	No
60713-003	115V	1	Polyamide 66, Polypropylene	No

Catalog Number	Input Voltage AC	Package Quantity	Material	Quick Ship
60713-002	230V	1	Polyamide 66, Polypropylene	No

ADDITIONAL PRODUCT DETAILS

24 В пост. тока по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE