

Модуль-заглушка AMC с вытяжной ручкой



Этот модуль-заглушка AdvancedMC состоит из передней панели из нержавеющей стали без светодиодных индикаторов и имеет прокладки для защиты от электромагнитных помех слева и снизу. Модуль-заглушка фиксируется на направляющей в шасси до щелчка пластикового носика. Модуль можно использовать для закрытия пустого слота, обеспечения ЭМС-экранирования и закрытия передней части для герметизации и защиты от утечек воздуха в шасси. Такие модули-заглушки можно использовать на носителях AdvancedMC и в слотах MicroTCA. Запирающая задвижка для этого не требуется.

CERTIFICATIONS



FEATURES

В соответствии со спецификацией AMC.0 R2.0

Экранированные модули-заглушки используются для закрытия неиспользуемых слотов

вытяжная ручка для извлечения модуля

Для направления воздушного потока в шасси можно использовать дополнительный дефлектор (с регулируемым воздушным потоком)

SPECIFICATIONS

Product Family: AdvancedMC
Type: Filler Module
Product Type: System Module

Table 1/1

Catalog Number	Design Feature	Material	Finish	Package Quantity	Quick Ship
20849-249	Mid-Size	Алюминий	Passivated	1	No

Catalog Number	Design Feature	Material	Finish	Package Quantity	Quick Ship
20849-022	Compact	Нержавеющая сталь		1	No
20849-250	Full-Size	Алюминий	Passivated	1	No
20849-106	Mid-Size	Нержавеющая сталь		1	No
20849-248	Mid-Size	Алюминий	Passivated	1	No
20849-025	Full-Size	Нержавеющая сталь		1	No
20849-251	Full-Size	Алюминий	Passivated	1	No
20849-024	Full-Size	Нержавеющая сталь		1	No
20849-107	Mid-Size	Нержавеющая сталь		1	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE