


Объединительная плата CPCI PlusIO



CompactPCI PlusIO сочетает в себе традиционный CompactPCI и новую высокоскоростную технологию CompactPCI Serial на одной объединительной плате. Системный слот CompactPCI PlusIO дополняет как параллельную шину PCI, так и слоты CompactPCI Serial с PCIe, USB, Ethernet и S-ATA.

CERTIFICATIONS



FEATURES

В соответствии с: PICMG 2.0 R3.0 CompactPCI Core Specification, Спецификация горячей замены PICMG 2.1 R2.0, PICMG 2.9 R1.0 System Management Bus Specification, PICMG 2.10 R1.0 Keying Specification, Спецификация CompactPCI PlusIO PICMG 2.30 R1.0, Спецификация PICMG CompactPCI Serial (CPCI-S.0 R1.0)

System slot in accordance with PICMG 2.30, 32-bit CPCI bus on P1, PCIe, S-ATA, USB

Периферийные слоты CompactPCI, 32-разрядные с Rear I/O на P2

Задняя панель ввода-вывода на слотах CompactPCI Serial по запросу

Слоты для плат периферийных устройств CompactPCI Serial с PCIe x1, S-ATA и USB

Полносвязный Ethernet на системном слоте и 2 слота CompactPCI Serial, поддерживает 1000Base-T и 10GBase-T

Параметр V (I/O) можно настроить на 3,3 В или 5 В (предустановлено 5 В)

SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-602	Объединительная плата	5	3U	CompactPCI PlusIO, CompactPCI Serial	Middle	4HP

CatalogNumber	Product Type	Number ofSlots	Rack Height	BackplaneType	System Slot	Slot Width
23007-601	Объединительная плата	8	3U	CompactPCI PlusIO, CompactPCI Serial	Middle	4HP

Table 2/3

Catalog Number	Voltage I/O	Connector Type	Power Connector Type	Utility Connector Type	Ширина мм	Package Quantity
23007-602	5V	HM 2.0, AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin	102.2mm	1
23007-601	5V	HM 2.0, AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin	161.3mm	1

Table 3/3

Catalog Number	Quick Ship
23007-602	No
23007-601	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE