

Система CPCI Serial с источником питания ATX, 4 U, 9 слотов

Система 4 U CompactPCI Serial с вертикальным каркасом для печатных плат на девять плат 3 U и одним встроенным источником питания ATX.



CERTIFICATIONS



FEATURES

Система соответствует IEC60297-3-101, -102, -103 IEEE 1101.1, 1101,10/11 объединительная плата соответствует PICMG CPCI-S.0

Система с вертикальным каркасом для печатных плат. Фронтальная плата: 3 U, глубина 160 мм, 9 слота

Объединительная плата с 9 слотами, 3 U, CompactPCI Serial (однозвездочная топология Ethernet-сети)

Отвод тепла с помощью вентиляторного блока с функцией горячей замены высотой 1 U

Источник питания ATX, 300 Вт

SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot
24579-420	System	9	19" Rack Mount	3 U CompactPCI Serial with Ethernet Star	PCIe Gen3	40W

CatalogNumber	Product Type	Number ofSlots	Type	BackplaneType	Data Transfer	Power per Slot
24579-415	System	9	19" Rack Mount	3 U CompactPCI Serial with Ethernet Star	PCIe Gen3	40W

Table 2/3

Catalog Number	Input Voltage AC	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O
24579-420	100 – 240V	Bottom to Top	4U	(1) ATX PSU	Да	Да
24579-415	100 – 240V	Bottom to Top	4U	(1) ATX PSU	Да	Нет

Table 3/3

Catalog Number	Complies With	Глубина мм	Высота мм	Package Quantity	Quick Ship
24579-420	PICMG CPCI-S.0 R2.0	275mm	177mm	1	No
24579-415	PICMG CPCI-S.0 R2.0	275mm	177mm	1	No

ADDITIONAL PRODUCT DETAILS

Модифицированные системы доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE