


DIN-рейка

DIN-рейка – это стандартная металлическая рейка, широко используемая для монтажа автоматических выключателей и промышленного контрольно-измерительного оборудования в аппаратных стойках.



FEATURES

С предварительно нарезанной длиной и перфорацией

Сталь с электрооцинкованной отделкой

Соответствие: стандарты EN 60715

SPECIFICATIONS

Product Type: DIN-рейка

Table 1/2

Catalog Number	Material	Высота мм	Длина мм	Finish	Package Quantity	Глубина мм
20118-878	Сталь	35mm	125mm	Zinc Plated	4	7.5mm
20118-879	Сталь	35mm	175mm	Zinc Plated	4	7.5mm
20118-872	Сталь	35mm	125mm	Zinc Plated	4	15mm
20118-880	Сталь	35mm	275mm	Zinc Plated	4	7.5mm
20118-890	Сталь	35mm	125mm	Zinc Plated	10	7.5mm
20118-873	Сталь	35mm	175mm	Zinc Plated	4	15mm

CatalogNumber	Material	Высота мм	Длина мм	Finish	Package Quantity	Глубина мм
20118-881	Сталь	35mm	375mm	Zinc Plated	4	7.5mm
20118-891	Сталь	35mm	175mm	Zinc Plated	10	7.5mm
20118-882	Сталь	35mm	475mm	Zinc Plated	4	7.5mm
20118-874	Сталь	35mm	275mm	Zinc Plated	4	15mm
20118-884	Сталь	35mm	125mm	Zinc Plated	10	15mm
20118-883	Сталь	35mm	575mm	Zinc Plated	4	7.5mm
20118-892	Сталь	35mm	275mm	Zinc Plated	10	7.5mm
20118-875	Сталь	35mm	375mm	Zinc Plated	4	15mm
20118-885	Сталь	35mm	175mm	Zinc Plated	10	15mm
20118-876	Сталь	35mm	475mm	Zinc Plated	4	15mm
20118-893	Сталь	35mm	375mm	Zinc Plated	10	7.5mm
20118-877	Сталь	35mm	575mm	Zinc Plated	4	15mm
20118-894	Сталь	35mm	475mm	Zinc Plated	10	7.5mm
20118-886	Сталь	35mm	275mm	Zinc Plated	10	15mm
20118-895	Сталь	35mm	575mm	Zinc Plated	10	7.5mm
20118-887	Сталь	35mm	375mm	Zinc Plated	10	15mm
20118-888	Сталь	35mm	475mm	Zinc Plated	10	15mm
20118-889	Сталь	35mm	575mm	Zinc Plated	10	15mm

Table 2/2

Catalog Number	Ширина мм	Quick Ship
20118-878	125mm	No
20118-879	175mm	No
20118-872	125mm	No
20118-880	275mm	No
20118-890	125mm	No
20118-873	175mm	No
20118-881	375mm	No
20118-891	175mm	No
20118-882	475mm	No
20118-874	275mm	No
20118-884	125mm	No
20118-883	575mm	No
20118-892	275mm	No
20118-875	375mm	No
20118-885	175mm	No
20118-876	475mm	No
20118-893	375mm	No
20118-877	575mm	No

Catalog Number	Ширина мм	Quick Ship
20118-894	475mm	No
20118-886	275mm	No
20118-895	575mm	No
20118-887	375mm	No
20118-888	475mm	No
20118-889	575mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE