

Вентилятор постоянного тока, 24 В, 119 x 119 x 25,5 мм, 171 м³/ч

CATALOG NUMBER

20713-172

Осевой вентилятор, 119 мм, с входом постоянного тока.
Запасная деталь для лотков вентиляторов 1 U.



CERTIFICATIONS



FEATURES

Осевой вентилятор постоянного тока 119 мм, с вилкой для подключения соединительного кабеля

PRODUCT ATTRIBUTES

Product Type: Fan

Works With: 19" Fan Trays

Ширина мм: 119mm

Длина мм: 119mm

Высота мм: 25.5mm

Voltage DC: 24V

Airflow: 171m³/h

Noise Level: 50.5dB(A)

Мощность W: 7W

Max Static Pressure: 50.5Pa

Ambient Temperature: 70°C

Net Weight: 0.2kg

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Соединительный кабель и защитная решетка заказываются отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE