


Ручка устройства для вставки/извлечения, тип IEL, серый рычаг, черная кнопка, верхняя, 10 шт.


CATALOG NUMBER

20817-622



Ручка для устройства вставки/извлечения, тип IEL в соответствии с IEEE 1101.10. Две из этих ручек могут выдерживать однократное рычажное усилие 700 Н (на пару).

CERTIFICATIONS



FEATURES

Нагрузка установки и извлечения до 700 Н (на пару ручек)

В соответствии с требованиями IEEE 1101.10 и IEC 60297-3-102

Микропереключатель можно установить

PRODUCT ATTRIBUTES

Package Quantity: 10

Handle Type: IEL; Top Front; Bottom Rear I/O

Flammability Rating: UL® 94V-0

Color: Серый

Complies With: EN 45545-2

Material: Polycarbonate

Product Type: Ручка


Type: Inserter/Extractor, Standard

Works With: Передние панели

ADDITIONAL PRODUCT DETAILS

Кодированные штекеры и микропереключатель заказываются отдельно.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE