


Ленточная ручка RatiopacPRO/-AIR, высота 3 U, 315 мм

CATALOG NUMBER

24571-308



Скобяная ручка для RatiopacPRO/-AIR с допустимой статической нагрузкой 20 кг. Возможность модернизации без механической обработки на корпусе.

CERTIFICATIONS



FEATURES

Допустимая статическая нагрузка 20 кг

Возможность модернизации без механической обработки на боковой панели корпуса

PRODUCT ATTRIBUTES

Rack Height: 3U

Глубина мм: 315mm

Package Quantity: 1

Handle Type: Strap

Product Family: RatiopacPRO; RatiopacPRO AIR

Product Type: Ручка

Works With: Coffrets

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE