


Альтернативная передняя панель для комбинированного монтажа, U-образного профиля, текстильной обработки, высота 6 U, ширина 2 HP

CATALOG NUMBER

30849-140



Передняя панель шириной 2 HP закрывает открытый слот. Передняя панель из U-образного профиля может сочетаться с текстильной ЭМС-прокладкой. Ее можно крепить винтами и шайбами. Из-за ширины 2 HP использование изоляционных трубок невозможно.

CERTIFICATIONS



FEATURES

Передняя панель из U-образного профиля 6 U, 2 HP, алюминий, 2,5 мм

Подготовлена для текстильной ЭМС-прокладки

PRODUCT ATTRIBUTES

Product Type: Передняя панель

Аксессуар Тип: Передняя панель

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Mounting: Screw-on Front

EMC Shielding: No (Retrofittable)

Gasket Type: Textile EMC

Material: Алюминий

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: Нет

Rack Height: 6U

Высота мм: 261.8mm

Rack Width: 2HP

Ширина мм: 9.8mm

Глубина мм: 2.5mm

Complies With: IEC 60297-3-101; IEEE 1101.1/10

Package Quantity: 1

Finish: Anodized; Passivated

Net Weight: 0.021kg

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE