


Guide Rail With Coding for CompactPCI/ VME64x, PC, 160 mm, 2 mm Groove Width, Grey

CATALOG NUMBER

64568-090



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

CERTIFICATIONS



FEATURES

НОВОЕ поколение с пластмассовыми направляющими кодирующего типа для надежной фиксации печатных плат или вставных блоков

Значительно повышенная устойчивость, благодаря оптимизированной конструкции и высококачественному материалу (поликарбонат)

«Не содержат галогенов», согласно IEC 61249-2-21

Могут быть закреплены на горизонтальных рельсах (алюминиевый экструдированный профиль) или на панелях толщиной 1,5 мм

Для более высоких требований в отношении ударных нагрузок и вибрации направляющие могут прикручиваться болтами к горизонтальной рейке (тип H и тип R)

Доступен дополнительный зажим ESD для проводящего контакта между печатной платой и горизонтальным рельсом

Температура хранения: от -40 °C до 130 °C

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

PRODUCT ATTRIBUTES

Material: Fiber-Reinforced Plastic
Color: Серый
Package Quantity: 1
Board Depth: 160mm
Groove Width: 2
Complies With: EN 45545-2
Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Product Type: Направляющие рельсы
Type: Coding
Works With: Блочный каркас; Coffrets; 19" Chassis; Системы

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE