

передняя панель, анодирование, Без экранирования, сборка на винтах

Анодированная передняя панель, вариант исполнения без экранирования, алюминий, 2,5 мм.



CERTIFICATIONS



FEATURES

Неполноразмерная передняя панель, алюминий, 2,5 мм

алюминий, анодирование

SPECIFICATIONS

Глубина мм (D):	2.5mm
Material:	Алюминий
Finish:	Anodized
Аксессуар Тип:	Передняя панель
Product Type:	Передняя панель
Type:	Front Panel without Handle

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-508	3U	3HP	1	Screw-on Front	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-481	3U	4HP	1	Screw-on Front	Anodized	Anodized
30818-741	6U	2HP	1	Screw-on Front	Anodized	Anodized
30807-510	3U	5HP	1	Screw-on Front	Anodized	Anodized
30807-482	3U	6HP	1	Screw-on Front	Anodized	Anodized
30807-509	3U	7HP	1	Screw-on Front	Anodized	Anodized
30807-484	3U	8HP	1	Screw-on Front	Anodized	Anodized
30807-483	3U	10HP	1	Screw-on Front	Anodized	Anodized
30807-777	6U	5HP	1	Screw-on Front	Anodized	Anodized
30807-485	3U	12HP	1	Screw-on Front	Anodized	Anodized
30807-752	6U	6HP	1	Screw-on Front	Anodized	Anodized
30807-501	3U	14HP	1	Screw-on Front	Anodized	Anodized
30807-833	6U	7HP	1	Screw-on Front	Anodized	Anodized
30807-779	6U	8HP	1	Screw-on Front	Anodized	Anodized
30807-487	3U	21HP	1	Screw-on Front	Anodized	Anodized
30807-753	6U	10HP	1	Screw-on Front	Anodized	Anodized
30807-755	6U	12HP	1	Screw-on Front	Anodized	Anodized
30807-496	3U	28HP	1	Screw-on Front	Anodized	Anodized
30807-758	6U	14HP	1	Screw-on Front	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-780	6U	16HP	1	Screw-on Front	Anodized	Anodized
30807-494	3U	42HP	1	Screw-on Front	Anodized	Anodized
30807-757	6U	21HP	1	Screw-on Front	Anodized	Anodized
30807-416	2U	84HP	1	Screw-on Front	Anodized	Anodized
30807-766	6U	28HP	1	Screw-on Front	Anodized	Anodized
30808-067	3U	63HP	1	Screw-on Front	Anodized	Anodized
30807-506	3U	84HP	1	Screw-on Front	Anodized	Anodized
30807-764	6U	42HP	1	Screw-on Front	Anodized	Anodized
30807-596	4U	84HP	1	Screw-on Front	Anodized	Anodized
30807-771	6U	63HP	1	Screw-on Front	Anodized	Anodized
30807-776	6U	84HP	1	Screw-on Front	Anodized	Anodized
30807-778	6U	4HP	1	Screw-on Front	Anodized	Anodized
30810-432	3U	2HP	1	Screw-on Front	Anodized	Anodized

Table 2/3

Catalog Number	Treated Edges	Complies With	EMC Shielding	Высота мм (H)	Ширина мм (W)	Certifications
30807-508	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	14.9mm	RoHS
30807-481	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	20mm	RoHS
30818-741	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	9.8mm	RoHS

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Высота мм (H)	Ширина мм(W)	Certifications
30807-510	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	25mm	RoHS
30807-482	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	30.1mm	RoHS
30807-509	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	35.2mm	RoHS
30807-484	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	40.3mm	RoHS
30807-483	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	50.5mm	RoHS
30807-777	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	25mm	RoHS
30807-485	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	60.6mm	RoHS
30807-752	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	30.1mm	RoHS
30807-501	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	70.8mm	RoHS
30807-833	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	35.2mm	RoHS
30807-779	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	40.3mm	RoHS
30807-487	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	106.3mm	RoHS
30807-753	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	50.5mm	RoHS
30807-755	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	60.6mm	RoHS
30807-496	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	141.9mm	RoHS

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Высота мм (H)	Ширина мм(W)	Certifications
30807-758	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	70.8mm	RoHS
30807-780	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	80.9mm	RoHS
30807-494	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	213mm	RoHS
30807-757	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	106.3mm	RoHS
30807-416	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	84mm	426.4mm	RoHS
30807-766	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	141.9mm	RoHS
30808-067	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	319.7mm	RoHS
30807-506	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	426.4mm	RoHS
30807-764	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	213mm	RoHS
30807-596	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	172.9mm	426.4mm	
30807-771	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	319.7mm	RoHS
30807-776	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	426.4mm	RoHS
30807-778	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	261.8mm	20mm	RoHS
30810-432	Да	IEC 60297-3-101, IEEE 1101.1/10	Нет	128.4mm	9.8mm	RoHS

Table 3/3

Catalog Number	Quick Ship
----------------	------------

30807-508	No
30807-481	No
30818-741	No
30807-510	No
30807-482	No
30807-509	No
30807-484	No
30807-483	No
30807-777	No
30807-485	No
30807-752	No
30807-501	No
30807-833	No
30807-779	No
30807-487	No
30807-753	No
30807-755	No
30807-496	No
30807-758	No

30807-780	No
30807-494	No
30807-757	No
30807-416	No
30807-766	No
30808-067	No
30807-506	No
30807-764	No
30807-596	No
30807-771	No
30807-776	No
30807-778	No
30810-432	No

ADDITIONAL PRODUCT DETAILS

Крепежный материал (втулки, винты с проточкой) заказывается отдельно.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE