

передняя панель, с экранированием, шарниры снизу

Передняя панель из U-образного профиля откидывается снизу для установки текстильного уплотнителя.



CERTIFICATIONS



FEATURES

Передняя панель из U-образного профиля откидывается под углом 135° (кроме RatiopacPRO)

Позволяет выполнять монтаж на горизонтальных рейках

с экранированием, передняя панель из U-образного профиля с текстильным ЭМС-уплотнителем

Подходит для блочных каркасов EuropacPRO и корпусов RatiopacPRO, PropacPRO, CompacPRO)

SPECIFICATIONS

Глубина мм (D):	2.5mm
Material:	Алюминий
Finish:	Anodized; Passivated
Аксессуар Тип:	Передняя панель
Product Type:	Передняя панель
Type:	Front Panel without Handle

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	EMC Gasket Type	Front Finish
----------------	-------------	------------	------------------	----------	-----------------	--------------

20848-608	3U	28HP	1	Hinged, Bottom	Textile	Anodized
20848-599	3U	42HP	1	Hinged, Bottom	Textile	Anodized
20848-600	3U	63HP	1	Hinged, Bottom	Textile	Anodized
20848-601	3U	84HP	1	Hinged, Bottom	Textile	Anodized
20848-605	4U	42HP	1	Hinged, Bottom	Textile	Anodized
20848-606	4U	63HP	1	Hinged, Bottom	Textile	Anodized
20848-607	4U	84HP	1	Hinged, Bottom	Textile	Anodized
20848-604	6U	84HP	1	Hinged, Bottom	Textile	Anodized
20848-602	6U	42HP	1	Hinged, Bottom	Textile	Anodized
20848-603	6U	63HP	1	Hinged, Bottom	Textile	Anodized
20848-696	6U	28HP	1	Hinged, Bottom	Textile	Anodized

Table 2/3						
Catalog Number	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм (H)	Ширина мм (W)
20848-608	Conductive	Her	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4mm	141.9mm
20848-599	Conductive	Her	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4mm	213mm
20848-600	Conductive	Her	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4mm	319.7mm
20848-601	Conductive	Her	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4mm	426.4mm
20848-605	Conductive	Her	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9mm	213mm

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Высота мм (H)	Ширина мм(W)
20848-606	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9mm	319.7mm
20848-607	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9mm	426.4mm
20848-604	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8mm	426.4mm
20848-602	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8mm	213mm
20848-603	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8mm	319.7mm
20848-696	Conductive	Нет	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8mm	141.9mm

Table 3/3


Catalog Number	Quick Ship
20848-608	No
20848-599	No
20848-600	No
20848-601	No
20848-605	No
20848-606	No
20848-607	No
20848-604	No
20848-602	No
20848-603	No

Catalog Number	Quick Ship
20848-696	No

ADDITIONAL PRODUCT DETAILS

Передняя панель снимается в открытом состоянии (> 135°)

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE