

Передняя панель Inрас, шарниры снизу

Нижняя откидная передняя панель может сочетаться с корпусами Inрас.



CERTIFICATIONS



FEATURES

Нижняя откидная передняя панель может сочетаться с корпусами Inрас

SPECIFICATIONS

Глубина мм:	2.5mm
Material:	Алюминий
Finish:	Anodized
Аксессуар Тип:	Передняя панель
Product Type:	Передняя панель

Table 1/2

Catalog Number	Rack Height	Package Quantity	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30828-085	2U	1	Anodized	Anodized	Нет	Нет
30828-097	6U	1	Anodized	Anodized	Нет	Нет

CatalogNumber	Rack Height	Package Quantity	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30828-091	4U	1	Anodized	Anodized	Нет	Нет
30828-088	3U	1	Anodized	Anodized	Нет	Нет

Table 2/2			
Catalog Number	Высота мм	Ширина мм	Quick Ship
30828-085	76mm	437mm	No
30828-097	253.8mm	437mm	No
30828-091	165mm	437mm	No
30828-088	120.5mm	437mm	No

ADDITIONAL PRODUCT DETAILS

Шарнир для передней панели заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE