

19-дюймовое шасси для монтажа в шкаф Interscale, Без перфорации



Пригодное для разнообразных задач 19-дюймовое шасси с интегрированной защитой от электромагнитных помех. На основе платформы nVent SCHROFF Interscale и в соответствии с IEC 60297-3-109.

CERTIFICATIONS



FEATURES

Настольный модульный корпус, состоящий из 4 компонентов

Разработано в соответствии с IEC 60297-3-109 (в стадии разработки IEC)

Встроенная защита от ЭМС

Степень защиты от внешних воздействий — до IP 30

Цвет RAL 7016

Модифицированные или изготавливаемые по спецификации заказчика корпуса доступны по запросу

SPECIFICATIONS

Material:	Сталь; Алюминий
Product Family:	Interscale
Product Type:	Small Form Factor Case
Type:	Solid
EMC Shielding:	Да

Table 1/2

Catalog Number	Rack Height	Глубина мм	Package Quantity	Usable Width	Mounting	Complies With
14821-105	1U	221.45mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-107	1U	310.35mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-307	3U	310.35mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-305	3U	221.45mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-207	2U	310.35mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-205	2U	221.45mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109

Table 2/2

Catalog Number	Finish	Quick Ship
14821-105	Aluminum-Zinc Plated, Powder Coated	No
14821-107	Aluminum-Zinc Plated, Powder Coated	No
14821-307	Aluminum-Zinc Plated, Powder Coated	No
14821-305	Aluminum-Zinc Plated, Powder Coated	No
14821-207	Aluminum-Zinc Plated, Powder Coated	No
14821-205	Aluminum-Zinc Plated, Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE