

Система МТСА.4 для 12 двойных полноразмерных модулей АМС



Система предназначена для высокопроизводительных и высокоэффективных режимов применения. Два вентиляторных модуля с функцией горячей замены, ЕММС, вытяжным охлаждением обеспечивают превосходное охлаждение слотов в передней и задней части. Скорость вентилятора регулируется через МСН. Благодаря отдельному слоту JSM модуль JTAG не занимает слоты для АМС. Система допускает подключение до четырех источников питания, что обеспечивает достаточное питание для требовательных приложений. На задней объединительной плате имеются сигнальные линии для тактовых и триггерных сигналов.

CERTIFICATIONS



FEATURES

В соответствии со спецификацией МТСА.4 R1.0

Система шириной 84 НР для 12 двойных полноразмерных модулей AdvancedMC, 2 одиночных полноразмерных МСН, и 4/2 одиночных полноразмерных модуля питания

6 слотов для двойных полноразмерных задних интерфейсных модулей (RTM)

1 одиночный полноразмерный слот для коммутационного модуля JTAG (JSM)

Объединительная плата с топологией Dual Star

В дополнительной комплектации частота вращения вентиляторов регулируется отдельно для передней и задней частей через МСН

2 вентиляторные кассеты с функцией горячей замены и управляющим контроллером вентиляторов (CU ЕММС)

Доступ к воздушным фильтрам спереди

SPECIFICATIONS

Table 1/3						
Catalog Number	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot
11890-170	System	12	19" Rack Mount	MTCA.4 Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-156	System	12	19" Rack Mount	CMS Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-152	System	12	19" Rack Mount	MTCA.4 Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-119	System	12	19" Rack Mount	CMS Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W

Table 2/3						
Catalog Number	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O	Complies With
11890-170	Front to Rear	9U	2 x (4) Single Full-size PM	Нет	Да	PICMG MTCA.4 R1.0
11890-156	Front to Rear	9U	2 x (4) Single Full-size PM	Нет	Да	PICMG MTCA.4 R1.0
11890-152	Bottom to Top	7U	2 x (4) Single Full-size PM	Нет	Да	PICMG MTCA.4 R1.0
11890-119	Bottom to Top	7U	2 x (4) Single Full-size PM	Нет	Да	PICMG MTCA.4 R1.0

Table 3/3			
Catalog Number	Глубина мм	Package Quantity	Quick Ship
11890-170	373mm	1	No
11890-156	373mm	1	No
11890-152	373mm	1	No
11890-119	373mm	1	No

ADDITIONAL PRODUCT DETAILS

Для работы системы требуется 2 источника питания.

Модифицированные системы доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE