

Комплект вставного модуля с трапецевидной ручкой, с экранированием, серый



Сменный модуль со статичной ручкой и U-образной передней панелью. Серая ручка собрана на передней панели. На U-образной панели возможна сборка текстильного уплотнителя.

CERTIFICATIONS



FEATURES

Передняя панель, U-образный профиль, экранированный

Ручка без функции извлечения

SPECIFICATIONS

Material:	Алюминий
Finish:	Anodized; Passivated
Product Type:	Передняя панель
Type:	Front Panel with Handle (PIU)
EMC Shielding:	Да

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	EMC Gasket Type
----------------	-------------	------------	------------------	-------------	----------	-----------------

20848-663	3U	3HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-664	3U	4HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-665	3U	5HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-666	3U	6HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-667	3U	7HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-668	3U	8HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-669	3U	10HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-670	3U	12HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-671	6U	3HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-672	6U	4HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-673	6U	5HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-674	6U	6HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-675	6U	7HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-676	6U	8HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile
20848-677	6U	10HP	1	Трапецевидн ой ручкой, антистатическ	Screw-on Front	Textile

20848-678	6U	12HP	1	Трапецевидной ручкой, антистатическ	Screw-on Front	Textile
-----------	----	------	---	-------------------------------------	----------------	---------

Table 2/3

Catalog Number	Front Finish	Rear Finish	Treated Edges	Flammability Rating	Complies With	Высота мм (H)
20848-663	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-664	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-665	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-666	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-667	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-668	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-669	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-670	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-671	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-672	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm

CatalogNumber	Front Finish	Rear Finish	Treated Edges	Flammability Rating	Complies With	Высота мм (H)
20848-673	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-674	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-675	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-676	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-677	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-678	Anodized	Etched	Нет	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm

Table 3/3

Catalog Number	Ширина мм (W)	Quick Ship
20848-663	14.9mm	No
20848-664	20mm	No
20848-665	25mm	No
20848-666	30.1mm	No
20848-667	35.2mm	No
20848-668	40.3mm	No
20848-669	50.5mm	No

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE