


PropacPRO Complete Desktop Case, с экранированием



Корпус nVent SCHROFF PropacPRO обеспечивает защиту электронных компонентов 19-дюймовых узлов, таких как вставные модули и европлаты. Алюминиевые литые рамы и профильные боковые панели гарантируют надежное решение. В стандартном исполнении используется ЭМС-экранирование.

CERTIFICATIONS



FEATURES

Настольный корпус, в сборе, конфигурация в соответствии с IEC 60297-3-101 для 19-дюймовых компонентов с экранированием

Вентиляционные отверстия в нижней крышке

Задняя панель с вентиляционными отверстиями

IP 20 в соответствии с IEC 60529

В соответствии с DIN EN 62368-1

SPECIFICATIONS

Static Load:	25kg
Product Type:	Корпус
Type:	Case for 19" Components
Product Family:	PropacPRO
EMC Shielding:	Да

Table 1/3

Catalog Number	Rack Height	Rack Width	Глубина мм	Package Quantity	Usable Height	Usable Width
24576-101	3U	28HP	266mm	1	112.3mm	148mm
24576-102	3U	28HP	326mm	1	112.3mm	148mm
24576-103	3U	42HP	266mm	1	112.3mm	219mm
24576-104	3U	42HP	326mm	1	112.3mm	219mm
24576-105	3U	42HP	386mm	1	112.3mm	219mm
24576-106	3U	63HP	266mm	1	112.3mm	326mm
24576-107	3U	63HP	326mm	1	112.3mm	326mm
24576-108	3U	63HP	386mm	1	112.3mm	326mm
24576-109	3U	84HP	266mm	1	112.3mm	432mm
24576-110	3U	84HP	326mm	1	112.3mm	432mm
24576-111	3U	84HP	386mm	1	112.3mm	432mm
24576-112	3U	84HP	446mm	1	112.3mm	432mm
24576-113	3U	84HP	506mm	1	112.3mm	432mm
24576-121	6U	84HP	326mm	1	245.7mm	432mm
24576-122	6U	84HP	446mm	1	245.7mm	432mm

Table 2/3

Catalog Number	Front Frame Construction	Cooling Option	Complies With	Finish	Высота мм	Material
24576-101	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий

CatalogNumber	Front Frame Construction	Cooling Option	Complies With	Finish	Высота мм	Material
24576-102	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-103	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-104	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-105	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-106	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-107	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-108	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-109	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-110	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-111	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-112	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-113	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Алюминий
24576-121	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	289mm	Алюминий
24576-122	Single Piece	Нет	IEC 60297-3-101	Passivated, Powder Coated	289mm	Алюминий

Table 3/3

Catalog Number	Protection Rating	Ширина мм	Quick Ship
24576-101	IP20	185.9mm	No
24576-102	IP20	185.9mm	No
24576-103	IP20	257mm	No

Catalog Number	Protection Rating	Ширина мм	Quick Ship
24576-104	IP20	257mm	No
24576-105	IP20	257mm	No
24576-106	IP20	363.7mm	No
24576-107	IP20	363.7mm	No
24576-108	IP20	363.7mm	No
24576-109	IP20	470.3mm	No
24576-110	IP20	470.3mm	No
24576-111	IP20	470.3mm	No
24576-112	IP20	470.3mm	No
24576-113	IP20	470.3mm	No
24576-121	IP20	470.3mm	No
24576-122	IP20	470.3mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE