

19-дюймовый источник питания перем. тока/пост. тока Maxpower, 100 Вт, одинарный



Pluggable 19" Power Supplies with H15 connector for fanless applications. С широким диапазоном входного напряжения (переменный ток) и одним выходным напряжением.

CERTIFICATIONS



FEATURES

Широкий диапазон входного напряжения 90 ... 254 В перем. тока и 100 ... 360 В пост. тока с активной коррекцией коэффициента мощности (PFC)

1 выходное напряжение

Сигнал "Выходное напряжение ОК"

Высокая удельная мощность

Встроенный развязывающий диод для операции резервирования

Равномерное распределение тока в параллельном режиме работы (CSB)

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Input Voltage AC	Мощность W	Number of Output Voltages	Voltage 1	Current 1
----------------	------	------------------	------------	---------------------------	-----------	-----------

13100-104	19" Switched-Mode	90 – 264V	99W	1	15V	6.6A
13100-103	19" Switched-Mode	90 – 264V	100W	1	12V	8.3A
13100-102	19" Switched-Mode	90 – 264V	80W	1	5V	16A
13100-105	19" Switched-Mode	90 – 264V	101W	1	24V	4.2A

Table 2/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
13100-104	3U	6HP	1	No
13100-103	3U	6HP	1	No
13100-102	3U	6HP	1	No
13100-105	3U	6HP	1	No

ADDITIONAL PRODUCT DETAILS

Передняя панель заказывается отдельно.

Выходные данные при напряжении сети > 190В перем. тока, Ta = 0 ...50°C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE