

Rack Safety Plus, 3 U, 208 / 240 V AC



FEATURES

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

208 V phase to phase or phase to neutral or 240 V phase to phase mains input

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

UL pending

SPECIFICATIONS

Function:	Emergency Stop
Inrush Current Limiter:	Нет
Residual Current Device:	Нет
Circuit Breaker Cover:	Нет
Works With:	Varistar CP; Novastar
Аксессуар Тип:	Энергораспределительные аксессуары

Table 1/2

Catalog Number	Product Type	Input Voltage AC	Number of Phases	EMC Filter	Surge Arrester	Rack Height
21272-003	Power Distributor	208 – 240V	1	Нет	Нет	3U
21272-001	Power Distributor	208 – 240V	1	Да	Да	3U

Table 2/2

Catalog Number	Socket Type	Package Quantity	Quick Ship
21272-003	IEC C13 lockable	1	No
21272-001	IEC C13, IEC C19	1	No

ADDITIONAL PRODUCT DETAILS

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE