

панель электропитания, IEC C13, с входом Wieland®



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Эта панель электропитания с алюминиевым шасси размером 1 U x 1 U легко интегрируется в шкаф. Разъем Wieland обеспечивает простую комбинацию с различными входными кабелями питания.

CERTIFICATIONS



FEATURES

Вход: штекер Wieland® GST 18

Установочная высота 1 U

В соответствии с IEC 60320

Горизонтальная или вертикальная установка

Выходы: розетки IEC 60320 C-13

Во время установки панель электропитания можно поворачивать во всех направлениях (с шагом 90°)

SPECIFICATIONS

Длина мм:	438.5mm
Material:	Алюминий; Polyamide
Product Type:	Панели электропитания

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
----------------	-------------	-----------------	------------------	------------	----------	------------------

60110-340	IEC C13	12	Нет	230V		1
60110-341	IEC C13	12	Нет	230V		1
60110-342	IEC C13	12	Нет	230V		1
60110-349	IEC C13	6	Нет	230V	Overcurrent Protection	1
60110-350	IEC C13	6	Нет	230V	Overcurrent Protection	1
60110-351	IEC C13	6	Нет	230V	Overcurrent Protection	1

Table 2/2				
Catalog Number	Color	Глубина мм	Finish	Quick Ship
60110-340	Серый	44mm	Anodized	No
60110-341	Черный	44mm	Anodized	No
60110-342	Красный	44mm	Anodized	No
60110-349	Серый	44mm	Anodized	No
60110-350	Черный	44mm	Anodized	No
60110-351	Красный	44mm	Anodized	No

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE