

Пружинные контакты для обжима



Пружинный контакт для обжима можно использовать вместе с разъемами DIN типа D с постоянным контактным сопротивлением.

CERTIFICATIONS



FEATURES

Пружинный контакт для обжима можно использовать вместе с разъемами DIN типа D

Газонепроницаемое и коррозионностойкое соединение

Постоянное контактное сопротивление с равномерным качеством обжима

SPECIFICATIONS

Works With: Connectors

Product Type: Spring Contact

Table 1/1

Catalog Number	Package Quantity	Connection Type	Quick Ship
21100-293	50	Crimping, 0.14 - 0.5 mm ²	No
21100-294	50	Crimping, 0.75 - 1.5 mm ²	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE