

Телескопическая направляющая Universal, 1 U

Телескопическая направляющая Universal с удлинением > 100 % и несущей способностью до 39 кг.



CERTIFICATIONS



FEATURES

Для боковой установки на 19" монтажный профиль (19" системная перфорация остается свободной для монтажа полок и ящиков)

Допустимая статическая нагрузка на пару 23 - 39 кг

С возможностью расцепления

Длина выдвижения > 100 %

Ширина направляющей k = 9,7 мм, макс. монтажная ширина выдвижной полки/выдвижного ящика w = 429 мм

SPECIFICATIONS

Material:	Сталь
Product Type:	Telescopic Slide
Finish:	Zinc Plated

Table 1/1

Catalog Number	Длина мм	Package Quantity	Static Load	Type	Quick Ship
----------------	----------	------------------	-------------	------	------------

20110-090	356mm	2	39kg	Universal	No
20110-091	406mm	2	36kg	Universal	No
20110-092	457mm	2	34kg	Universal	No
20110-093	508mm	2	32kg	Universal	No
20110-094	559mm	2	29kg	Universal	No
20110-095	610mm	2	27kg	Universal	No
20110-096	660mm	2	23kg	Universal	No
20110-097	711mm	2	23kg	Universal	No

ADDITIONAL PRODUCT DETAILS

Телескопические рейки Universal также могут быть установлены без дополнительных компонентов в нестандартных системах, отличных от 19-дюймовых шкафов.

Для установки на 19-дюймовой панели необходимо дополнительно заказать монтажный комплект.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE