


Телескопическая направляющая Universal, 2 U

Телескопическая направляющая Universal с удлинением > 100 % и несущей способностью до 61 кг.



CERTIFICATIONS



FEATURES

Ширина направляющей $k = 16$ мм, макс. установочная ширина расширения/выдвижного ящика $w = 417$ мм

Боковая установка на 19-дюймовых стойках (19-дюймовая поверхность остается свободной для фиксации выдвижения/выдвижного ящика)

Блокировка при полном выдвижении

Длина выдвижения > 100 %

Допустимая статическая нагрузка на пару 46 - 61 кг

SPECIFICATIONS

Material:	Сталь
Product Type:	Telescopic Slide
Finish:	Zinc Plated

Table 1/1

Catalog Number	Длина мм	Package Quantity	Static Load	Type	Quick Ship
----------------	----------	------------------	-------------	------	------------

20110-100	305mm	2	61kg	Universal	No
20110-101	356mm	2	60kg	Universal	No
20110-102	406mm	2	58kg	Universal	No
20110-105	559mm	2	52kg	Universal	No
20110-103	457mm	2	57kg	Universal	No
20110-104	508mm	2	55kg	Universal	No
20110-106	610mm	2	50kg	Universal	No
20110-107	660mm	2	48kg	Universal	No
20110-108	711mm	2	46kg	Universal	No

ADDITIONAL PRODUCT DETAILS

Для установки на 19-дюймовую панель монтажный комплект заказывается отдельно. Телескопические рейки Universal также могут быть установлены без дополнительных компонентов в нестандартных системах, отличных от 19-дюймовых шкафов.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE