

Varistar CP IP 20 Cabinet, стеклянная передняя дверь, стальная задняя дверь



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FEATURES

Степень защиты IP 20

Со стеклянной передней дверью

Двери с одноточечным запирающим, боковые панели на быстроразъемных фиксаторах

Допустимая статическая нагрузка 1600 кг

SPECIFICATIONS

Product Type: Cabinet

Protection Rating: IP20

Material: Сталь

Table 1/3

Catalog Number	Rack Height	Высота мм	Frame Color	Ширина мм	Frame Color Code	Cladding Material
10630-040	42U	2000mm	Black Grey	600mm	RAL 7021	Сталь
10630-038	38U	1800mm	Black Grey	600mm	RAL 7021	Сталь

CatalogNumber	Rack Height	Высота мм	Frame Color	Ширина мм	Frame Color Code	Cladding Material
10630-039	42U	2000mm	Black Grey	600mm	RAL 7021	Сталь
10630-037	38U	1800mm	Black Grey	600mm	RAL 7021	Сталь

Table 2/3

Catalog Number	Глубина мм	Cladding Color	Package Quantity	Cladding Color Code	Complies With	Finish
10630-040	600mm	Black Grey	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Powder Coated
10630-038	800mm	Black Grey	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Powder Coated
10630-039	600mm	Black Grey	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Powder Coated
10630-037	600mm	Black Grey	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Powder Coated

Table 3/3

Catalog Number	Frame Material	Static Load	Quick Ship
10630-040	Сталь	1600kg	No
10630-038	Сталь	1600kg	No
10630-039	Сталь	1600kg	No
10630-037	Сталь	1600kg	No

ADDITIONAL PRODUCT DETAILS

Возможно дополнительное оснащение дверей поворотной ручкой.

Дополнительные сведения о размерах и исполнениях доступны. Цоколь следует заказывать отдельно. Для монтажа полок и направляющих рельсов необходимы дополнительные монтажные панели/профили.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE