

Серверный шкаф Varistar CP



Сварная стальная рама для высоких статических нагрузок. Подходит для интеграции 19-дюймового ИТ-оборудования.

FEATURES

Предварительно сконфигурирован, готовый к использованию шкаф

Допустимая статическая нагрузка до 1600 кг, динамическая 1000 кг

Степень защиты IP 20

Возможна установка различного ИТ-оборудования

Встроенные панели для управления воздушными потоками для охлаждения спереди назад

Легко интегрируется в систему изолированного коридора

SPECIFICATIONS

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Сталь

Table 1/2

Catalog Number	Rack Height	Высота мм	Cladding Material	Ширина мм	Cladding Color	Глубина мм
10630-018	42U	2000mm	Сталь	800mm	Black Grey	1200mm

CatalogNumber	Rack Height	Высота мм	Cladding Material	Ширина мм	Cladding Color	Глубина мм
10630-020	47U	2200mm	Сталь	800mm	Black Grey	1200mm
10630-017	42U	2000mm	Сталь	600mm	Black Grey	1200mm
10630-019	47U	2200mm	Сталь	600mm	Black Grey	1200mm
10630-023	42U	2000mm	Сталь	600mm	Black Grey	1200mm
10630-024	42U	2000mm	Сталь	800mm	Black Grey	1200mm
10630-025	47U	2200mm	Сталь	600mm	Black Grey	1200mm
10630-026	47U	2200mm	Сталь	800mm	Black Grey	1200mm

Table 2/2

Catalog Number	Type	Package Quantity	Dynamic Load	Finish	Material	Quick Ship
10630-018	Standard	1	1000kgf	Powder Coated	Сталь	No
10630-020	Standard	1	1000kgf	Powder Coated	Сталь	No
10630-017	Standard	1	1000kgf	Powder Coated	Сталь	No
10630-019	Standard	1	1000kgf	Powder Coated	Сталь	No
10630-023	Side-by-Side	1	1000kgf	Powder Coated	Сталь	No
10630-024	Side-by-Side	1	1000kgf	Powder Coated	Сталь	No
10630-025	Side-by-Side	1	1000kgf	Powder Coated	Сталь	No
10630-026	Side-by-Side	1	1000kgf	Powder Coated	Сталь	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE