

Varistar CP Swing Frame for 600 mm Width



The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° movement and flexible pivot point.

FEATURES

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks (maximum depth 200 mm)

120° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

SPECIFICATIONS

Ширина мм: 600mm
Product Type: Cabinet/Rack Frame
Material: Сталь

Table 1/2						
Catalog Number	Rack Height	Package Quantity	Color	Color Code	Finish	Высота мм
21630-668	24U	1	Black Grey	RAL 7021	Powder Coated	1200mm
21630-678	47U	1	Black Grey	RAL 7021	Powder Coated	2200mm
21630-676	42U	1	Black Grey	RAL 7021	Powder Coated	2000mm
21630-674	38U	1	Black Grey	RAL 7021	Powder Coated	1800mm
21630-672	33U	1	Black Grey	RAL 7021	Powder Coated	1600mm
21630-670	29U	1	Black Grey	RAL 7021	Powder Coated	1400mm

Table 2/2		
Catalog Number	Protection Rating	Quick Ship
21630-668	IP20	No
21630-678	IP20	No
21630-676	IP20	No
21630-674	IP20	No
21630-672	IP20	No
21630-670	IP20	No

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE