

# Telescoping Screw Gun Box Bracket



## CERTIFICATIONS



## FEATURES

Can mount multiple boxes

Notched and marked for easy identification and bending

Improved design with stamped inch markings and pilot holes accelerates precise box conduit mounting between studs

Pilot holes allow easy box attachment with a screwdriver

Requires only a screw gun to install

Can be mounted to face or inside of stud

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly

Unique, one-piece, break apart design

## SPECIFICATIONS

**Finish:** Pregalvanized

**Material:** Сталь

Table 1/1

| Catalog Number | Article Number | Stud Spacing | Box Depth |
|----------------|----------------|--------------|-----------|
|----------------|----------------|--------------|-----------|

|          |        |              |                    |
|----------|--------|--------------|--------------------|
| TSGB16   | 187190 | 280 - 458 mm | 38mm, 54mm         |
| TSGB1624 | 187199 | 400 - 635 mm | 38mm, 54mm, 63.5mm |
| TSGB24   | 187191 | 432 - 660 mm | 38mm, 54mm, 63.5mm |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

