

# Special Track Work Mold Only, Power, 250 kcmil Ropelay, Left Hand

## Data Solutions

### CATALOG NUMBER

**PBJT52WLHM**



### FEATURES

Replacement molds designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

### PRODUCT ATTRIBUTES

Material: Graphite

Bond Terminal Style: J

Rail Type: Crane Rail Profiles

Conductor Size: 250 kcmil Ropelay

Conductor Outer Diameter, Nominal: 19.05mm

Welder Style: T5

Orientation: Left Hand

Mold Only: Да

Welding Material: PB90 or PB90PLUSF80, Sold Separately

Handle Clamp: B323BX, Sold Separately

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**